


Rittal – The System.

Faster – better – everywhere.



DK 5302.002

Air baffle plate

State: 11/09/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 5302.002 - Air baffle plate for VX IT 482.6 mm (19") mounting angles, dynamic

To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system.



Features

| | |
|---------------------|---|
| Model No. | DK 5302.002 |
| Product description | For selectively boosting the energy efficiency of a climate control system. |
| Benefits | Vertical brush strip for collision-free shielding with installed rail systems on the outer mounting level. |
| Applications | To separate the hot/cold zones within an enclosure with aisle containment or when using an LCP system. |
| Material | Sheet steel Blanking panel: Plastic, UL 94-HB, halogen-free Brush strip: Plastic, UL 94-HB |
| Surface finish | Spray-finished |
| Colour | RAL 9005 |
| Supply includes | 2 vertical trim panels 2 horizontal trim panels 4 brush strips 4 cellular PU foam pieces Assembly parts |

Features

| | |
|-----------------------|--|
| Assembly instruction | <p>The vertical trim panels with brush strip may be fitted on both the front and rear 482.6 mm (19") mounting angles for partitioning.</p> <p>The horizontal trim panels with brush strips can only be mounted on the front 482.6 mm (19") mounting angles.</p> <p>482.6 mm (19") mounting cut-outs integrated within the partitioning areas may optionally be sealed with the supplied blanking panels, or used to install additional components or for cable routing. Please see the product-specific scope of supply.</p> |
| To fit | <p>Width: = 600 mm</p> <p>Height: = 1,800 mm</p> |
| Packs of | 1 pc(s). |
| Net weight | 0.001 |
| Gross weight | 0.001 |
| Customs tariff number | 73269098 |
| EAN | 4028177955172 |
| E-Number Sweden | E7282574 |
| ETIM 9 | EC000331 |
| ECLASS 8.0 | 27189272 |