
Rittal - The System.

Faster – better – everywhere.





DK 5501.460 Slide rail, 1 U, depth-variable

State: 27/10/2025 (Source: rittal.com/uae-en)



DK 5501.460 - Slide rail, 1 U, depth-variable for VX IT, TE, TX CableNet

For mounting between a front and a rear pair of mounting angles.





Features

Model No.	DK 5501.460
Benefits	Tool-free, time-saving one-man assembly from the enclosure front All three mounting holes in the EIA system punchings are available for screw-fastening the equipment. Alternatively, direct screw fastening in the TE 8000 to the 482.6 mm (19") system punchings is also possible
Applications	For mounting on the front mounting level To support heavy installed equipment To adapt to individual distances between 482.6 mm (19") levels
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
Installation options	482.6 mm (19") L mounting angles, front and rear 482.6 mm (19") mounting frames front and rear for 482.6 mm (19") mounting angles, standard
Load capacity	800 N
Note	Effective contact surface 25 mm per side
To fit	Enclosure type: VX IT TE TX CableNet

© Rittal 2025

Features

Distance between levels	400 - 600 mm
Packs of	2 pc(s).
Net weight	2.164
Gross weight	2.34
PCF per pack (cradle-to-gate)	9 kg CO2 eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	73269098
EAN	4028177679016
E-Number Sweden	E7239696
ETIM 9	EC002620
ECLASS 8.0	27189261

© Rittal 2025 3

Tender text

482.6 mm (19") - slide rails, depth-variable
Depth-variable slide rails for L-shaped mounting
angles and similar shapes of mounting angles.
For mounting between a pair of mounting angles
and to support heavy installed equipment.
Distance between 482.6 mm (19") levels from
400-600 mm, load capacity 80 kg.
The slide rails have vent holes across the entire
depth to support the climate control of integral
components.

Tool-free, time saving one-man assembly from the enclosure front.

Locate, pull-out, snap into position.

All three mounting holes in the 482.6 mm (19") system punchings are available for screw-fastening the equipment.

Material: Sheet steel

Surface finish: Zinc-plated Model No. DK: 5501.460 Manufacturer: Rittal

© Rittal 2025 4