


Rittal – The System.

Faster – better – everywhere.



CP 6321.000

Operating housing for desktop TFT up to 24"

State: 15/12/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CP 6321.000 - Operating housing for desktop TFT up to 24"

Integral VESA 75/100 locator. Effective, attractive protection for commercially available desktop TFTs up to 24" in the formats 16:9/16:10. High protection category IP 65.

Features

| | |
|-------------------------------------|--|
| Model No. | CP 6321.000 |
| Design | Viewing window with single-pane safety glass |
| Product description | For the installation of commercially available desktop TFTs with a screen diagonal of up to 24" in the formats 16:9/16:10. |
| Material | Enclosure and door: Sheet steel Handle strips: Aluminium Cover caps: Plastic Viewing window: Single-pane safety glass TFT holder: Sheet steel |
| Surface finish | Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Handle strip: Natural anodised |
| Colour | Enclosure and door: RAL 7035 Handle strip: Natural anodised Cover caps: similar to RAL 7024 |
| Supply includes | Enclosure with cut-out and reinforcement for support arm connection Ø 130 mm Viewing window Holder for desktop TFT with VESA 75/100 locator Side handle strips and cover caps Rear door with r/h hinge Cam lock with 3 mm double-bit insert |
| Dimensions | Width: 650 mm Height: 450 mm Depth: 155 mm |
| IP protection category to IEC 60529 | IP 65 |

Features

| | |
|-----------------------|---|
| Number of locks | 1 |
| Note | <p>The support arm connection and door hinge may be swapped over by rotating the enclosure</p> <p>Optional: Support arm connection Ø 130 mm, preformed off-centre in the reinforcement plate, easily drilled out</p> <p>Lock insert may be exchanged for 27 mm lock inserts, type A, lock cylinder, plastic handles and T handles, type B</p> |
| Basic material | Aluminium |
| Lock | <p>Lock version: Cam</p> <p>Number of locks: 1</p> <p>Lock insert: 3 mm double-bit</p> |
| Packs of | 1 pc(s). |
| Net weight | 16.468 |
| Gross weight | 17.335 |
| Customs tariff number | 94032080 |
| EAN | 4028177697324 |
| ECLASS 8.0 | 27180505 |

Approvals

| | |
|--------------|--|
| Explanations | <p>Declaration of conformity</p> <p>Declaration of conformity UK</p> |
|--------------|--|