


Rittal – The System.

Faster – better – everywhere.



CX 6700.000

CX pedestal

State: 11/07/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



CX 6700.000 - CX pedestal

CX pedestals, four widths and two different depths provide the basis for every console solution. The AX lock plate ensures a uniform appearance, and two-part gland plates are included with the supply for simple cable routing.



Features

Model No.	CX 6700.000
Design	Pedestal
Material	Enclosure: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm, all-round foamed-in PU seal Mounting plate: Sheet steel, 2.5 mm
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure open at top Door or double-door at front, with 3-point locking system Mounting plate Gland plates Lock: 3 mm double-bit
Dimensions	Width: 600 mm Height: 675 mm Depth: 400 mm

Features

Dimensions mounting plate (W x H)	520 mm x 625 mm
Number of doors	1
Door opening angle	130°
IK Code	IK10
Note	A cover plate is required to seal the pedestal A desk unit and desk unit cover plate are required for 2-part console assembly A desk unit and console are required for 3-part console assembly.
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 1 NEMA 12
Basic material	Sheet steel
Number of locks	1
Lock version	3-point lock system
Lock insert	3 mm double-bit
Lock	Lock version: 3-point lock system Number of locks: 1 Lock insert: 3 mm double-bit
Packs of	1 pc(s).
Net weight	31 kg
Gross weight	33 kg
Customs tariff number	94032080
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504
Product description	CX console system, pedestal, WxHxD: 600x675x400 mm, sheet steel

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
