Rittal – The System.

Faster – better – everywhere.

# DK 7030.070

# CMC III mounting units

State: 05/03/2026 (Source: rittal.com/uae-en)

ENCLOSURES | POWER DISTRIBUTION | CLIMATE CONTROL | IT INFRASTRUCTURE | SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

# DK 7030.070 - CMC III mounting units

To accommodate CMC III components.





## Features

| | |
|---|---|
| Model No. | DK 7030.070 |
| Design | For PU, PU Compact, control units, CMC III CAN bus unit and CMC III power pack. |
| Product description | Depending on the design, the mounting unit can accommodate 1 or 3 Processing Units / sensor units etc. The 482.6 mm version (19" levels) can accommodate 3 units. The enclosure frame version can accommodate 1 unit. |
| Benefits | Fire protection: Self-extinguishing to UL 94 HB |
| Applications | Accommodation of CMC III components. |
| Function principle | CMC III Processing Unit<br>CMC III Processing Unit Compact<br>CMC III control unit<br>CMC III power pack<br>CMC III LTE unit<br>CMC III door control module |
| Material | Sheet steel |
| Surface finish | Zinc plated, passivated |
| Supply includes | Blanking cover |
| Number of locations | 3 |

# Features

| | |
|---|---|
| Installation options | 482.6 mm (19") level |
| Dimensions | Width: 482.6 mm<br>Depth: 141 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.8 kg |
| Gross weight | 1.02 kg |
| Customs tariff number | 73269098 |
| ETIM 9 | EC002627 |
| ECLASS 8.0 | 27189253 |
| Product description | DK CMC III mounting units, Accommodation of CMC III components, For 482.6 mm (19"), WHD: 138x40x132 mm |

# Tender text

7030.070
CMC III mounting unit, 1 U
Packs of 1
Used to mount PU, PU Compact, control units, CMC III CAN bus unit and CMC III power pack.
The mounting unit can accommodate up to three units and is attached in the 19? frame. The components to be mounted are plugged in at the front and automatically lock into place. In the rear section of the system there is an integrated option for fastening the CMC III cable clamp straps 7030.087.
Technical specifications:
Width: 482.6 mm (19?)
Height: 44.25 mm (1 U)
Depth: 141 mm
Material: Zinc-plated sheet steel
Temperature application range:
0 °C to 55 °C
Humidity range:
5% to 95% relative humidity, non-condensing
Included in the pack: Mounting unit and assembly parts

© Rittal 2026