

# Rittal – The System.

Faster – better – everywhere.



## DK 7030.202

## CMC III access control

State: 03/09/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# DK 7030.202 - CMC III access control

CMC III unit for controlling and monitoring access to enclosures.

## Features

|                      |  |
|----------------------|--|
| Model No.            | DK 7030.202  |
| Product description  | CMC III unit for controlling and monitoring access to enclosures. One handle and one reader unit may be connected to one CMC III access control. The handles can be linked to various numerical codes or transponder cards via the CMC III Processing Unit/ Compact website, which means that all the handles connected to a CMC III Processing Unit/Compact can be controlled with just one reader unit. The integral infrared sensor also ensures that the status of the controlled door (open/closed) is monitored. |
| Function principle   | For connecting one handle and one reader unit to monitor a door<br>Integral IR access sensor   |
| Design               | Record of every access and each time the door is opened, with user information and time stamp<br>Supports one central reader unit per CMC III system<br>Fixed allocation between handles and reader units<br>Four-eyes principle<br>Central administration of access rights across all systems and locations with RiZone<br>Activating the LED display in the handle   |
| Material             | Plastic<br>Front: Smooth<br>Enclosure: Textured  |
| Surface finish       | Front: Smooth<br>Enclosure: Textured   |
| Colour               | Front: RAL 9005<br>Enclosure: RAL 7035   |
| Supply includes      | CMC III access control<br>Mounting plate<br>Assembly parts   |
| Interface bus system | 2 x RJ45 CAN bus   |

# Features

|  |  |
|--|--|
| Interfaces                                   | RJ12<br>Flat-pin connector                     |
| No. of participants per IoT interface (max.) | 5  |
| No. of participating PU compact (max.)       | 2  |
| No. of participating PU (max.)               | 16   |
| Dimensions                                   | Width: 110 mm<br>Height: 30 mm<br>Depth: 40 mm |
| Operating temperature range                  | 0 °C...55 °C                                   |
| Ambient humidity (non-condensing)            | 5...95 %                                       |
| Packs of                                     | 1 pc(s).                                       |
| Net weight                                   | 0.175  |
| Gross weight                                 | 0.183  |
| Customs tariff number                        | 85311095                                       |
| EAN  | 4028177925847                                  |
| ETIM 9                                       | EC002627                                       |
| ECLASS 8.0                                   | 27189253                                       |

# Approvals

|              |                           |
|--------------|---------------------------|
| Approvals    | UL + C-UL (listed)        |
| Explanations | Declaration of conformity |