
### Rittal - The System.

Faster – better – everywhere.





### DK 7140.535

# Cable management panel with brush strip

State: 10/12/2025 (Source: rittal.com/uae-en)




## DK 7140.535 - Cable management panel with brush strip 482.6 mm (19")

With cut-out 390 x 40 mm (2 U) or 390 x 20 mm (1 U) with brush insert, accommodation facility for cable clamp straps.







### **Features**

| Model No.           | DK 7140.535  |
|---------------------|--|
| Product description | For convenient, simple cable routing between two areas separated<br>by a 482.6 mm (19") mounting level, for example, between the front<br>and rear areas of the 482.6 mm (19") mounting level. |
| Applications        | For locking and simultaneous cable routing in installation zones to the 1 U, 482.6 mm (19") mounting standard  |
| Material            | Sheet steel<br>Brush strip: Plastic, UL 94-HB  |
| Surface finish      | Spray-finished   |
| Colour              | RAL 7035   |
| Mounting cut-out    | Width:390 mm<br>Height:20 mm   |
| Dimensions          | Width: 482.6 mm  |
| Units               | 1 U  |
| Packs of            | 1 pc(s).   |
| Net weight          | 0.43   |
| Gross weight        | 0.475  |
|                     |  |

© Rittal 2025

#### **Features**

| Customs tariff number | 73269098      |
|-----------------------|---------------|
| EAN                   | 4028177166608 |
| E-Number Sweden       | E7239716      |
| ETIM 9                | EC000322      |
| ECLASS 8.0            | 27400604      |

### Tender text

482.6 mm (19") cable entry panel, 1 U

482.6 mm (19") cable entry panel, 1 U; the cables are fed in through the cutout (410 x 18 mm). The cutout also has an edge protector and a brush insert that protects against dust

Material: Sheet steel Colour: RAL 7035

© Rittal 2025 3