

Rittal – The System.

Faster – better – everywhere.



DK 7161.000 Telescopic slides

State: 10/09/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7161.000 - Telescopic slides for component shelves, for mounting on the VX enclosure frame and for upgrading existing VX and TS applications

For retrospectively converting fixed component shelves to full withdrawal by exchanging the fastening bolts or mounting rails (heavy-duty version) for the telescopic slides.

Features

| | |
|------------------------------------|---|
| Model No. | DK 7161.000 |
| Product description | Fixed component shelves are easily converted to full withdrawal. For this purpose, the existing fastening bolts or mounting rails (heavy-duty version) are exchanged for the telescopic slides. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Suitable for component shelf depth | 600 mm |
| Load capacity | 50 kg |
| Note | For installation and locking on a 25 mm pitch pattern in the enclosure depth. |
| Packs of | 2 pc(s). |
| Net weight | 2.16 |
| Gross weight | 2.34 |
| PCF per pack (cradle-to-gate) | 9 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |
| EAN | 4028177126039 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |

Tender text

Telescopic slides for 600 mm deep base unit

The telescopic are installed inbetween the installation kit and the 600 mm deep component shelf. The telescopic slides can hold a load up to a maximum of 50 kg and have double locks.

Material: Sheet steel, zinc-plated, passivated

For use with component shelf depths of: 600 mm