

Rittal – The System.

Faster – better – everywhere.



DK 7824.490

All-glass door, vertically divided

State: 02/04/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7824.490 - All-glass door, vertically divided for DK-TS

To replace existing doors. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced.

Features

| | |
|-----------------------|--------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Model No. | DK 7824.490 |
| Product description | With 180° hinges and locking rod including comfort handle with security lock no. 3524 E. Thanks to the minimal rotation radius of the individual doors, the distance between individual bayed enclosure suites may be reduced. |
| Material | Frame elements: Aluminium Viewing window: Single-pane safety glass, 5 mm |
| Colour | Frame: RAL 7035 Viewing windows: Tinted |
| Supply includes | Assembly parts |
| Note | Not to be used in conjunction with a swing frame |
| To fit | Enclosure type: DK-TS Width: 800 mm Height: 2,000 mm |
| Packs of | 1 pc(s). |
| Net weight | 24.951 kg |
| Gross weight | 26.264 kg |
| Customs tariff number | 76169990 |
| ECLASS 8.0 | 27182204 |
| Product description | DK All-glass door, vertically divided, WxH: 800x2000 mm, 180° hinges, Comfort handle incl. Security lock 3524 E |

Tender text

Vertically divided all-glass door, including 180° hinges

180° hinges and locking rod including comfort handle with 3124 E security lock.

Material: sheet steel, spray finished in RAL 7035; 5 mm single-pane safety glass, surrounding frame made from aluminium; tinted, parsol grey safety glass

Enclosure W x D: 800 mm x 2000 mm