

Rittal – The System.

Faster – better – everywhere.



DK 7826.750

Vent cover

State: 02/07/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7826.750 - Vent cover for VX, VX IT

For connecting sealed racks to a ventilation system. The stepped connection is suitable for standard pipe diameters 150 mm and 200 mm, thereby ensuring effective cooling due to targeted air exchange inside the rack.

Features

| | |
|-----------------------|--|
| Model No. | DK 7826.750 |
| Product description | The ideal addition for incorporating sealed racks into an existing central climate control system. The stepped connection is suitable for standard pipe diameters, thereby ensuring effective cooling thanks to targeted air exchange inside the rack. |
| Material | PET-G |
| Colour | Transparent |
| Supply includes | Assembly parts |
| Ø Hose connection | 150 mm 200 mm |
| Note | Required cut-out in the roof plate (W x D): 380 x 230 mm |
| Dimensions | Width: 450 mm Height: 144 mm Depth: 300 mm |
| Packs of | 1 pc(s). |
| Net weight | 0.959 kg |
| Gross weight | 0.96 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000331 |
| ECLASS 8.0 | 27189272 |
| Product description | DK vent cover, for hot air extraction to a ventilation system, WHD: 450 x 144 x 300 mm, cut-outs W x D max. 380 x 230 mm, PET-G, transparent |

Tender text

Vent cover

The ideal addition for incorporating sealed racks into an existing central climate control system.

The stepped connection is suitable for standard pipe diameters 150 mm and 200 mm.

Maximum cut-out on roof plate: 380 x 230 mm.

Material: PET-G, transparent

Supply includes: Assembly parts

Dimensions W x H x D: 450 x 144 x 300 mm