


Rittal – The System.

Faster – better – everywhere.



DK 7828.961

Component shelf, heavy duty

State: 08/12/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7828.961 - Component shelf, heavy duty for network enclosures TS with L-shaped mounting angles

For static installation between two 482.6 mm (19 1/8") mounting levels, they are located directly onto the L-shaped mounting angles, load capacity: 75 kg.

Features

Model No.	DK 7828.961
Product description	For static installation between two 482.6 mm (19 1/8") mounting levels. The component shelf is located directly onto the L-shaped mounting angles.
Material	Sheet steel
Surface finish	Zinc-plated
Colour	RAL 7035
Supply includes	Assembly parts
Distance between mounting levels	598 mm
Load capacity	75 kg surface load, static
Note	Not suitable for combination with telescopic slides.
Dimensions	Width: 507.5 mm Height: 20 mm Depth: 580 mm
Packs of	1 pc(s).
Net weight	3.65
Gross weight	3.85
Customs tariff number	94039910
EAN	4028177233300
ECLASS 8.0	27189261

Tender text

Component shelf for 2 mounting levels, static installation

Component shelf for static installation between two 19" mounting levels.

Mounted directly on the mounting angles.

The component shelf uses ventilation slots, which ensures economical air exchange between the separate layers.

For mounting on L-shaped mounting angles.

Load capacity: 75 kg surface load

Material: Sheet steel

Spray finish: RAL 7035

For distance between levels: 600 mm