


Rittal – The System.

Faster – better – everywhere.



DK 7856.191 PSM socket modules

State: 08/09/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



DK 7856.191 - PSM socket modules

The various modules may be inserted into the support rail in any combination.

Features

Model No.	DK 7856.191
Design	non-switchable
Product description	The modular system facilitates basic configuration of the racks, thanks to a vertical support rail with single-/3-phase infeed. The various socket modules to supply the active components may be snap-fitted into the support rail. The various modules, earthing pins, IEC320 etc. may be inserted into the support rail in any combination. This is easily achieved, even by non-electricians, thanks to the shock hazard protected plug & play system.
Material	Section: Aluminium, anodised Socket inserts: Plastic (PA6 GF 30 V1)
Rated operating voltage	110 V – 230 V AC, 50/60 Hz
Rated current	16 A
Rated current (max.)	16 A
Required number of module slots	1
Dimensions	Width: 52 mm Height: 250 mm Depth: 45 mm
Operating temperature range	5 °C...45 °C
Ambient humidity (non-condensing)	5...95 %
Sockets	4 x CH (type J, SEV 1011)
Packs of	1 pc(s).
Net weight	0.29
Gross weight	0.34
Customs tariff number	85369001

Features

EAN	4028177692381
ETIM 9	EC000330
ECLASS 8.0	27142604