Rittal - The System.

Faster – better – everywhere.






DK 7859.081 PSM Zero-U-Space

State: 12/11/2025 (Source: rittal.com/uae-en)



DK 7859.081 - PSM Zero-U-Space

Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.



Features

Model No.	DK 7859.081
Product description	Modular PDU for space-saving integration in the zero-U space between side panel and 482.6 mm (19") mounting level in 800 mm wide IT racks.
Material	Aluminium section, natural anodised
Length	1,695 mm
Length of connection cable	3 m
Type of electrical connection	fixed/CEE
Qty.	1
Phases per infeed	3~
Rated current (max.)	16 A
Module slots (max.)	6
IP protection category to IEC 60 529	IP 20
Dimensions	Length: 1,695 mm

© Rittal 2025

Features

To fit	Enclosure type: VX IT Height: ≥ 2,000 mm
Operating temperature range	5 °C45 °C
Ambient humidity (non- condensing)	1090 %
Packs of	1 pc(s).
Net weight	4
Gross weight	4.3
Customs tariff number	85369001
EAN	4028177956636
ETIM 9	EC002762
ECLASS 8.0	27371306

Approvals

Explanations	Declaration of conformity
--------------	---------------------------

© Rittal 2025 3