

Rittal – The System.

Faster – better – everywhere.



SZ 7967.000

Spacer

State: 08/08/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 7967.000 - Spacer for roof plate

To raise the roof for ventilation purposes, in three different heights. Not suitable for crane transportation.



Features

| | |
|-------------------------------|--|
| Model No. | SZ 7967.000 |
| Product description | To raise the roof for ventilation purposes, in three different heights. |
| Material | Hexagon steel section |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Assembly instruction | Not suitable for combination with 482.6 mm (19") mounting frame Not suitable for crane transportation |
| Dimensions | Height: 50 mm |
| Dimensions | Thread: M12 |
| To fit | Enclosure type: VX TS |
| Packs of | 4 pc(s). |
| Net weight | 0.444 |
| Gross weight | 0.539 |
| PCF per pack (cradle-to-gate) | 2.1 kg CO2 eq (Cat B) |
| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
| Customs tariff number | 73269098 |

Features

| | |
|-----------------|---------------|
| EAN | 4028177186934 |
| E-Number Sweden | E7239676 |
| ETIM 9 | EC002625 |
| ECLASS 8.0 | 27189234 |

Tender text

Spacers, 50 mm

Material: Hexagonal sectional steel, zinc-plated,
passivated,