


Rittal – The System.

Faster – better – everywhere.



VX 8001.219

Gland plate

State: 26/05/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



VX 8001.219 - Gland plate for VX, VX IT, VX SE

For individual configuration of the floor space. Potential equalisation is provided via assembly components and earthing points.

Features

| | |
|-----------------------|--|
| Model No. | VX 8001.219 |
| Product description | For individual configuration of the floor space. Potential equalisation is achieved via assembly components and earthing points. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Note | At least one sliding plate is required to fully seal a base opening. For two-door enclosures, one pack is sufficient for one half of the enclosure |
| Dimensions | Width: 690 mm Depth: 237.5 mm |
| To fit | Enclosure type: VX VX IT VX SE CX one-piece console CX pedestal Width: = 800 mm |
| Packs of | 1 pc(s). |
| Net weight | 2 kg |
| Gross weight | 2.3 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC002620 |
| ECLASS 8.0 | 27189261 |
| Product description | VX Gland plate, WD: 800x237,5 mm |

Approvals

Approvals

UL + C-UL (listed)