Rittal – The System.

Faster – better – everywhere.





TS 8166.235

Side panel, screw-fastened, sheet steel

State: 04/11/2025 (Source: rittal.com/uae-en)



TS 8166.235 - Side panel, screw-fastened, sheet steel for TS, TS IT

Side panels, screw-fastened, sheet steel, for TS.

Features

Model No.	TS 8166.235	
Benefits	Automatic potential equalisation and higher EMC protection due to enclosure panel holders with earthing insert Easy positioning with the location aid Earthing bolt with contact surface	
 Material	Sheet steel, 1.5 mm	
Surface finish	Dipcoat-primed, powder-coated on the outside	
Colour	RAL 7035	
Supply includes	Assembly parts	
Note	Enclosure panel holders may optionally be fitted from the inside of outside of the enclosure Area available for population: External dimension – 100 mm	
To fit	Enclosure type: TS TS IT Height: 1,600 mm Depth: 600 mm	
IP protection category to IEC 60 529	IP 55	
Basic material	Sheet steel	
Packs of	2 pc(s).	
Net weight	22.4	
Gross weight	23.6	
Customs tariff number	94039910	
EAN	4028177205192	

© Rittal 2025

Features

E-Number Sweden	E7282538	
ETIM 9	EC002524	
ECLASS 8.0	27182101	

Tender text

Surface finish

Dipcoat-primed, powder-coated in textured RAL 7035 on the outside

Colour

RAL 7035

Supply includes

2 side panels,

12 enclosure panel holders,

12 countersunk screws,

12 hexagon screws and

12 contact elements.

Product notes

Enclosure panel holders may optionally be fitted from the inside or outside of the enclosure.

Area available for population: External dimension - 100 mm.

Material

Sheet steel 1.5 mm

Protection category to EN 60 529/10.91

IP 55 to EN 60 529/10.91

© Rittal 2025 3