


Rittal – The System.

Faster – better – everywhere.



TS 8612.560

TS punched section with mounting flange, 23 x 73 mm

State: 06/09/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8612.560 - TS punched section with mounting flange, 23 x 73 mm

The alternative to the TS punched section with mounting flange 17 x 73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure.



Features

| | |
|-----------------------|---|
| Model No. | TS 8612.560 |
| Product description | The alternative to the TS punched section with mounting flange 17 x 73 mm, with punchings for captive nuts/threaded blocks instead of the slotted holes top and bottom. Simply locate and secure. |
| Material | Sheet steel |
| Surface finish | Zinc-plated |
| Supply includes | Assembly screws |
| Installation options | On the vertical TS, VX SE enclosure section |
| To fit | Enclosure type: the inner mounting level To fit width/depth: 600 mm |
| Packs of | 4 pc(s). |
| Net weight | 2.544 |
| Gross weight | 2.74 |
| Customs tariff number | 73269098 |
| EAN | 4028177237391 |
| ETIM 9 | EC002625 |

Features

ECLASS 8.0

27189234