Rittal - The System.

Faster - better - everywhere.



TS 8612.780 TS punched rail 25 x 38 mm

State: 26/11/2025 (Source: rittal.com/uae-en)



TS 8612.780 - TS punched rail 25 x 38 mm

For heavy installations, with attachment holes. Installation options on the vertical TS enclosure section.





Features

Model No.	TS 8612.780	
Product description	For heavy installations, with attachment holes.	
Material	Sheet steel, 3.0 mm	
Surface finish	Zinc-plated	
Supply includes	Assembly screws	
Installation options	On the vertical TS, VX SE enclosure section With 9 mm round holes all round on a 25 mm pitch pattern For the external mounting angle of support rails, system support rails, C rails 30/15, cable clamp rails (right angle section), own assemblies	
Note	In conjunction with the snap-on nut, particularly well-suited for dynamic connections	
To fit	To fit width/depth: 800 mm	
Packs of	2 pc(s).	
Net weight	2.488	
Gross weight	2.687	
Customs tariff number	73269098	
EAN	4028177429154	

© Rittal 2025

Features

ETIM 9	EC002620	
ECLASS 8.0	27189261	

© Rittal 2025 3