


# Rittal – The System.

Faster – better – everywhere.



## VX 8617.100

### Punched section with mounting flange, 23 x 64 mm

State: 27/07/2025 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.100 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



## Features

Model No.	VX 8617.100
Product description	For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.
Benefits	Simply locate into the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX SE installation options	In enclosure depth 300 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility
AX installation options	In enclosure width/height 300 mm, in conjunction with rail for interior installation AX and base configuration rail for AX
AX stainless steel installation options	In enclosure width/height 300 mm, in conjunction with the base configuration rail

# Features

VX base/plinth installation options	In base/plinth width/depth 300 mm on the base/plinth trim panels, in conjunction with base/plinth installation bracket In base/plinth width/depth 400 mm for mounting on the base/plinth corner pieces
To fit	Enclosure type: VX IT VX SE AX Suitable for width or height or depth: 300 mm
To fit	Base/plinth system VX
Packs of	4 pc(s).
Net weight	1.08
Gross weight	1.118
Customs tariff number	73269098
EAN	4028177829107
ETIM 9	EC002620
ECLASS 8.0	27189234