

**Rittal – The System.**

Faster – better – everywhere.



**VX 8617.200**

**Punched section with mounting  
flange, 23 x 64 mm**

State: 25/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# VX 8617.200 - Punched section with mounting flange, 23 x 64 mm for VX, VX IT, VX SE, AX plastic

For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.



## Features

Model No.	VX 8617.200
Product description	For variable, individual interior installation of the enclosure frame on the inner mounting level, and for installation in compact enclosures.
Benefits	Simply locate into the system punchings and screw-fasten System punchings on all four sides With slots at the top and bottom for cage nuts, for attaching your own components via metric screws
Material	Sheet steel
Surface finish	Zinc-plated
Supply includes	Assembly parts
VX installation options	In enclosure height 2000 mm, on the inner mounting level
VX SE installation options	In enclosure height 2000 mm, on the inner mounting level, in conjunction with adaptor rail for VX compatibility
To fit	Enclosure type: VX VX IT VX SE Suitable for width or height or depth: 2,000 mm

# Features

---

Packs of	4 pc(s).
Net weight	7.56 kg
Gross weight	8.62 kg
PCF per pack (cradle-to-gate)	44.86
Customs tariff number	73269098
ETIM 9	EC002620
ECLASS 8.0	27189234
Product description	VX Punched section, with mounting flange 23 x 64 mm, for inner mounting level

# Approvals

---

Explanations	PCF-declaration
--------------	-----------------