

Rittal – The System.

Faster – better – everywhere.



TS 8701.050

Base/plinth trim panels, side, 100 mm

State: 08/09/2025 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



TS 8701.050 - Base/plinth trim panels, side, 100 mm

Stainless steel for base/plinth components front and rear

For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trims may be used. Base/plinth trims may be installed rotated through 90° in order to stabilise bayed base/plinth components.

Features

| | |
|-----------------------|--|
| Model No. | TS 8701.050 |
| Product description | For mounting between the base/plinth components. At 200 mm height, two 100 mm base/plinth trim panels may be used. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 400 |
| Supply includes | 2 base/plinth trim panels Assembly parts |
| Assembly instruction | Base/plinth trim panels, side, 100 mm, may be installed rotated through 90° to stabilise bayed base/plinth components. The base/plinth baying bracket is required for this purpose |
| Dimensions | Height: 100 mm |
| To fit | Enclosure type: TS: = 500 mm |
| Packs of | 2 pc(s). |
| Net weight | 2.002 |
| Gross weight | 2.202 |
| Customs tariff number | 94039910 |
| EAN | 4028177300071 |
| ETIM 9 | EC000721 |
| ECLASS 8.0 | 27182003 |