

Rittal – The System.

Faster – better – everywhere.



PC 8800.920

Base/plinth, stationary

State: 16/01/2026 (Source: rittal.com/uae-en)



FRIEDHELM LOH GROUP

PC 8800.920 - Base/plinth, stationary for PC, IW

Design-coordinated with the enclosures, height 100 mm, with front projection.

Features

Model No.	PC 8800.920
Product description	Design-coordinated with the enclosures, with front projection.
Material	Sheet steel, 2.0 mm
Colour	RAL 7035 Design component, front: RAL 7015
Supply includes	1 design component, front 1 base/plinth component, rear 2 base/plinth trim panels, side
Dimensions	Height: 100 mm
To fit	Enclosure type: PC IW Width: = 600 mm Depth: = 600 mm
Suitable for depth	600 mm
Packs of	1 pc(s).
Net weight	11.92
Gross weight	13.02
PCF per pack (cradle-to-gate)	49.5 kg CO ₂ eq (Cat B)
Note on PCF category	Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
Customs tariff number	94039910
EAN	4028177266926
ETIM 9	EC000721
ECLASS 8.0	27182003