

# Rittal – The System.

Faster – better – everywhere.



TS 8900.050

Isolator door cover (US version), for  
TS

State: 12/06/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES



FRIEDHELM LOH GROUP

# TS 8900.050 - Isolator door cover (US version), for TS

TS isolator door cover (US version), in accordance with US regulations, only in conjunction with actuator lever for master switches.



## Features

---

Model No.	TS 8900.050
Product description	Including main door lock for safety locking of enclosures and bayed enclosure suites in accordance with US regulations, only in conjunction with actuator lever for master switches: Allen Bradley 1494 F-M1/P1/S1 and 140 U-K-FCX04, Square D 9422 A1, Siemens actuator Max-Flex drives for compact circuit-breakers in the SENTRON series (ED, FD, LD, JD. Not for Siemens ACB 3VL) US Model No.: FHOH, General Electric TDA types 1 and 2, Moeller NZM-XSHGVR 12-NA.

---

# Features

---

Benefits	<p>In combination with operating mechanism, adjacent door latch, interconnecting rods meets the requirements of UL 508 A.</p> <p>Compact design with a width of just 100 mm.</p> <p>May be mounted instead of a side panel. With this cover, all standard single-door TS 8 enclosures may be configured as isolator door enclosures. The complete installation surface of the enclosure is retained.</p> <p>May be mounted optionally on the left or right of the enclosure.</p> <p>In conjunction with the integrable TS mounting plate infill, the mounting surface of the main enclosure can be enlarged by around 100 mm in width.</p>
Material	Sheet steel
Surface finish	Powder-coated
Colour	RAL 7035
Supply includes	Main door lock, cover plate and assembly parts.
IP protection category to IEC 60529	IP 55
Protection category NEMA	NEMA 12
Dimensions	Width: 100 mm Height: 2,000 mm Depth: 500 mm
Packs of	1 pc(s).
Net weight	22.2 kg
Gross weight	24.7 kg
Customs tariff number	73269098
ECLASS 8.0	27180101

# Approvals

---

Approvals	UL + C-UL (listed)
-----------	--------------------