Rittal - The System.

Faster – better – everywhere.





DK 9055.312 Monitor/keyboard unit

State: 18/11/2025 (Source: rittal.com/uae-en)



DK 9055.312 - Monitor/keyboard unit with 17" TFT display and VGA/DVI connection

1 U chassis with 17" TFT display, English or German keyboard layout, with telescopic slides.



Features

Model No.	DK 9055.312	
Product description	The unit is housed in a pull-out drawer. The monitor can be flipped up and the drawer latches into the end position. This means that the unit only requires 1 U in the 482.6 mm (19") rack.	
Benefits	Analog and digital video input	
	Cables are safely routed in the energy chain	
	Lockable at the front	
	Simple, one-man installation.	
Colour	RAL 7035	
Supply includes	Monitor/keyboard unit, 1 U	
	VGA cable	
	DVI cable	
	USB cable	
	Earthing-pin mains cable	
	with 17" TFT display and VGA/DVI connection	
	2 PS/2 cables	
	Keyboard	
	with integral touchpad	
Rated operating voltage	100 V - 240 V, 1~, 50 Hz/60 Hz	
Max. power consumption with closed monitor unit	1 W	

© Rittal 2025

Features

Max. power consumption in operation	32 W	
Interfaces	VGA (D-Sub HD 15-pole)	
	DVI	
	1 x USB	
	PS/2	
Connector (type)	IEC 320 connector C14	
Layout	US English	
Dimensions	Width: 482.6 mm	
	Depth: 680 mm	
Operating temperature range	5 °C45 °C	
Installation dimensions	Installation depth (min.): 680 mm	
	Installation depth (max.): 850 mm	
Display features	Diagonal: 432 mm (17")	
	Format: 4:3	
	Contrast ratio: Contrast ratio approx. 1000:1	
	Display brightness: 350 cd/m²	
	Resolution of display: 1280 x 1024 pixels	
	Number of colours: 16,700,000	
Packs of	1 pc(s).	
Net weight	15.85	
Gross weight	17.25	
Customs tariff number	85286200	
EAN	4028177638389	
ETIM 9	EC001428	
ECLASS 8.0	19200201	

Approvals

Explanations	Declaration of conformity	
--------------	---------------------------	--

© Rittal 2025 3