

Rittal – The System.

Faster – better – everywhere.



RX 9360.613

RiLineX CB component adaptor

State: 05/07/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9360.613 - RiLineX CB component adaptor

RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting with semi-automatic adjustment of the bar thickness between 5 and 10 mm. Version for cable outlet at the top.



Features

Model No.	RX 9360.613
Design	universal
Benefits	Direct mounting of moulded-case circuit-breakers (MCCBs) on the board Snap-on mounting up to 250 A and simple adjustment to busbar thickness 5/10 mm Fast, simple pre-assembly of standard market switch types outside of the enclosure
Material	Polyamide (PA 6) Fire protection corresponding to UL 94
Colour	RAL 9005 RAL 35745
IP protection category to IEC 60529	IP 2XB
Rated impulse withstand voltage Uimp	8 kV

Features

Rated voltage	690 V AC 600 V AC (UL)
Rated insulation voltage U_i	1,000 V
Contamination level	3
Number of poles	3-pole
Cable outlet	Top
Type of electrical connection	Screw M8
Cross-section	15 mm ² 6 mm ²
To fit manufacturer (model)	Our selection aid, available in the Downloads section, helps you to easily find a matching component adaptor.
To fit busbar system	RiLineX RiLine60
Fundamental frequency	50...60 Hz
Ambient humidity (non-condensing)	10...90 %
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Operating temperature range	-25 °C...55 °C
Storage temperature range	-25 °C...75 °C
Dimensions	Width: 109 mm Height: 251.4 mm Depth: 62.8 mm
Fire load	8.086 MJ/m ²
Packs of	1 pc(s).
Net weight	1.47 kg
Gross weight	1.473 kg
PCF per pack (cradle-to-gate)	9.96
Customs tariff number	39269097

Features

Product description	RiLineX CB component adaptor (3-pole, max. 250 A) for 60 mm busbar systems. The device width is 105 mm. The "Universal" variant with U nuts offers maximum flexibility for switch mounting. The adaptor features tool-free snap-on mounting. Version for cable outlet at the top.
---------------------	---

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity PCF-declaration

Tender text

RiLineX CB component adaptor (Universal Fix)

RiLineX CB component adaptor
for 60 mm busbar systems.

Fastening is carried out using u-nuts in
the two adjustable support rails.

For voltages up to 690 V AC and 690 V DC.

IEC and UL approved.

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 250 A

Connection: 90 mm²

Cable outlet: top

Dimensions: 108 mm x 251 mm x 51 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9360613