

Rittal – The System.

Faster – better – everywhere.



RX 9364.004 RiLineX fuse holder

State: 01/06/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE



SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



RX 9364.004 - RiLineX fuse holder

Compact RiLineX class CC fuse holder for 60 mm busbar systems. For class CC cylindrical fuse (30 A) with optical LED fuse monitoring. For reliable contact of cylindrical fuses, the device has special fuse holders that are lockable in the open state and sealable in the closed state. Spring terminal blocks up to 6 mm² at an angle of 45° enable easier conductor connection. The device is suitable for tool-free snap-on mounting with semi-automatic busbar adjustment for 5 and 10 mm. Includes electronic fuse monitoring.



Features

Model No.	RX 9364.004
Benefits	<ul style="list-style-type: none">Snap-on mounting and simple adjustment for busbar thickness (5/10 mm)For Class CC fuse to UL 248-4UL-listed, approved to UL 4248Innovative swivel mechanism, selective replacement of individual fuse inserts supportedReadily accessible push-in connections in the lower sectionFuse removal tools included with the supplyCan be locked and prepared for a lead seal with electronic fuse monitoring
Material	<ul style="list-style-type: none">Polyamide (PA 6)Fire protection corresponding to UL 94-V0
General colour	<ul style="list-style-type: none">RAL 9005RAL 35745
Rated current (max.)	30 A

Features

Type of electrical connection	Spring terminal
Rated operating voltage	600 V AC
Electrical ratings UL (SCCR)	200 kA - 600 V, Fuse Class CC max. 30 A, JDDZ/7
Number of poles	3-pole
Dimensions	Width: 27 mm Height: 263 mm Depth: 123.5 mm
Connection of round conductors, fine wire with wire end ferrule	1.5 - 6 mm ²
To fit busbars	15 x 5/10 20 x 5/10 30 x 5/10
Fuse inserts	Class CC
For fuse type (class)	Fuse Class CC
Packs of	4 pc(s).
Net weight	1.2 kg
Gross weight	1.406 kg
Customs tariff number	85369095

Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------

Tender text

RiLineX Bus-mounting fuse base (Typ Fuseholder with EFM)

Bus-mounting fuse base for class CC cylindrical fuse.

Fuses insters are operated individually or

collectively via a front slide.

Optical fuse monitoring with LED.

Conductor connection via tension spring terminals.

Rated voltage 600 V AC.

With UL approval

Product information

Number of poles: 3

Busbar dimensions: 15/20/30 mm x 5/10 mm

Rated current: 30 A

Connection: 1,5 - 6 mm²

Cable outlet: bottom

Feature: Electronic fuse monitoring

Dimensions: 27 mm x 263 mm x 95 mm (WxHxD)

Manufacturer: Rittal GmbH & Co. KG

Type: 9364004