

Rittal – The System.

Faster – better – everywhere.



SV 9614.000

Mini-PLS component adaptor

State: 04/07/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9614.000 - Mini-PLS component adaptor

Maximum rated current from 12 A to 100 A.

Features

Model No.	SV 9614.000
Material	Polyamide Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Connection cables (AWG)	AWG 12
Rated operating voltage	690 V, 3~
Rated current max.	25 A
Dimensions	Width: 54 mm Height: 160 mm
Support rails Qty/height	1 / 7.5 mm
To fit manufacturer (model)	ABB Eaton Siemens MS325 MS450 max. 25 A MS451 max. 25 A PKZM4 bis 25 A PKE65 bis 25 A 3RV10 31 bis 25 A
Packs of	1 pc(s).
Net weight	0.27 kg
Gross weight	0.318 kg
Copper weight (kg per piece)	0.041
Customs tariff number	85369095
ETIM 9	EC001531
ECLASS 8.0	27370304

Features

Product description

SV Mini-PLS component adaptor, 25 A, 690 V, 3-pole, connection cable AWG 12, WH: 54x160 mm, support rail H: 7,5 mm

Approvals

Approvals

UR + C-UR (recognized)

Explanations

Declaration of conformity
Declaration of conformity UK