

Rittal – The System.

Faster – better – everywhere.



SV 9635.700

NH fuse-switch disconnecter

State: 16/04/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9635.700 - NH fuse-switch disconnecter Size 000

For RiLine Compact busbar system.



Features

Model No.	SV 9635.700
Function principle	To protect connected equipment Integral test holes provide measurement access to the contact parts of the fuse inserts For cable outlet at the top, the NH fuse-switch disconnecter must be mounted on the board rotated through 180°
Material	Polyamide Fire protection corresponding to UL 94-V0 Contact tracks: Silver-plated hard copper
Colour	RAL 7035
Test specification	IEC/DIN EN 60 947-3
For NH size	000
Rated operating current max.	125 A
Rated operating voltage	440 V (DC), 3~ 690 V (AC), 3~
Number of poles	3-pole
Cable outlet	Top/bottom
Type of electrical connection	Box terminal

Features

Connection of round conductors	2.5 - 50 mm ²
Clamping area for laminated copper bars (W x H)	10 x 10 mm
Dimensions	Width: 49.5 mm Height: 174.5 mm Depth: 96 mm
Packs of	1 pc(s).
Net weight	0.52 kg
Gross weight	0.562 kg
Copper weight (kg per piece)	0.145
Customs tariff number	85369095
ETIM 9	EC001040
ECLASS 8.0	27371401
Product description	LV HRC fused interrupter, size 000, 690 V (RiLine Compact)