

**Rittal – The System.**

Faster – better – everywhere.



# SV 9665.760

## Cable entry gland

State: 23/05/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9665.760 - Cable entry gland for roof plate

Cable entry glands for roof plates, with metric knockouts, sealing membranes, entry glands, or sealed.



## Features

|                                     |   |
|-------------------------------------|---|
| Model No.                           | SV 9665.760   |
| Design                              | 2 x M25/32/40, 1 x M32/40/50, 2 x M40/50/63           |
| Product description                 | For simple, secure cable entry in the roof zone.      |
| Material                            | Insulating material                                   |
| Colour                              | RAL 7035  |
| Supply includes                     | Seal included   |
| No. of metric knockouts             | 2 x M25/M32/M40<br>1 x M32/M40/M50<br>2 x M40/M50/M63 |
| Dimensions                          | Width: 250 mm<br>Depth: 160 mm                        |
| IP protection category to IEC 60529 | IP 55   |
| Packs of                            | 1 pc(s).  |
| Net weight                          | 0.25 kg   |
| Gross weight                        | 0.281 kg  |
| Customs tariff number               | 39269097  |
| ETIM 9                              | EC000211  |

# Features

---

ECLASS 8.0

27142421

---

Product description

SV Cable entry gland, 2xM25/32/40, 1xM32/40/50, 2xM40/50/63,  
insulating material