

# Rittal – The System.

Faster – better – everywhere.



## SV 9676.982 Threaded bolts

State: 14/08/2025 (Source: [rittal.com/uae-en](https://www.rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SV 9676.982 - Threaded bolts for sliding blocks and sliding nuts

For attaching connection components such as ring terminals.

## Features

Model No.	SV 9676.982
Product description	For individual connection options.
Material	Steel
Supply includes	Assembly parts
To fit busbars	Maxi-PLS 60
Dimensions	Thread: M12 Thread length: 50 mm
Packs of	8 pc(s).
Net weight	0.4
Gross weight	0.478
Customs tariff number	73181535
EAN	4028177606920
ETIM 9	EC002349
ECLASS 8.0	23110302

## Approvals

Approvals	UL + C-UL (listed)
-----------	--------------------