

Rittal – The System.

Faster – better – everywhere.



SV 9677.715 Component adaptor

State: 31/03/2026 (Source: rittal.com/uae-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 9677.715 - Component adaptor screw attachment

For circuit-breakers from ABB, Eaton, Schneider Electric and Siemens. For bar systems with 185 mm centre-to-centre spacing.

Features

| | |
|---|--|
| Model No. | SV 9677.715 |
| Material | Polyamide Fire protection corresponding to UL 94-V0 |
| Colour | RAL 7035 |
| For bar systems with centre-to-centre spacing | 185 mm |
| Cable outlet | Bottom |
| Installation type | Screw attachment |
| Number of poles | 3-pole |
| Rated current max. | 1,600 A |
| Rated operating voltage | 690 V, 3~ |
| Note | Cable outlet: Switch outlet or as outgoing cable from the switchgear Suitable for the use of switchgear with front screw terminal For attaching to busbars with holes. Please ensure that there is no cover section installed in the vicinity of the device. |
| Dimensions | Width: 300 mm Height: 652 mm |
| To fit busbars | Height: 10 mm |
| To fit manufacturer (model) | ABB (Tmax T7 - 1250 A/1600 A) Eaton (NZM4 - 1250 A/1600 A) Schneider Electric (NS - 1250 A/1600 A) Siemens (3VA27 - 1250 A/1600 A) |
| Packs of | 1 pc(s). |
| Net weight | 19.34 kg |
| Gross weight | 21.4 kg |

Features

| | |
|------------------------------|---|
| Copper weight (kg per piece) | 14.749 |
| Customs tariff number | 85369095 |
| ETIM 9 | EC001531 |
| ECLASS 8.0 | 27370304 |
| Product description | SV Component adaptor, 1600 A, 690 V, 3-pole, 185 mm, screw attachment |

Approvals

| | |
|--------------|---|
| Approvals | UL + C-UL (listed) |
| Explanations | Declaration of conformity Declaration of conformity UK |