## Rittal - The System.

Faster – better – everywhere.





# SV 9677.905 Connection adaptor

State: 30/10/2025 (Source: rittal.com/uae-en)



# SV 9677.905 - Connection adaptor

For the connection of round conductors. For bar systems with 185 mm centre-to-centre spacing.

#### **Features**

| Model No.   | SV 9677.905  |
|---|--|
| Material  | Chassis: Fibreglass-reinforced polyester Fire protection corresponding to UL 94-V0                       |
| Colour  | RAL 7035   |
| Supply includes                                   | Contact hazard protection cover plate  |
| For bar systems with centre-to-<br>centre spacing | 185 mm   |
| Cable outlet                                      | Top/bottom   |
| Type of electrical connection                     | Screw M12  |
| Number of poles                                   | 3-pole   |
| Rated current max.                                | 1,400 A  |
| Rated operating voltage                           | 690 V, 3~  |
| Note  | When using components on busbars with contact hazard protection cover, the contact terminal must be used |
| Dimensions  | Width: 100 mm<br>Height: 960 mm  |
| Connection of round conductors                    | 6 - 300 mm²  |
| To fit busbars                                    | Height: 10 mm  |
| Packs of  | 1 pc(s).   |
| Net weight  | 11   |
| Gross weight                                      | 11.5   |
| Copper weight (kg per piece)                      | 4.41   |
| Customs tariff number                             | 85369010   |
| EAN   | 4028177705296  |

© Rittal 2025

## Features

| ETIM 9     | EC001531 |
|------------|----------|
| ECLASS 8.0 | 27370304 |

# **Approvals**

| Explanations | Declaration of conformity    |
|--------------|------------------------------|
|              | Declaration of conformity UK |

© Rittal 2025 3