Rittal – The System.

Faster – better – everywhere.





SV 9681.204 Perforated mounting strip

State: 14/12/2025 (Source: rittal.com/uae-en)



SV 9681.204 - Perforated mounting strip for partial door

For retrospective external mounting on partial doors, with 25 mm hole pitch pattern for mounting individual items on the rear of doors such as cable ducts, conduit holders, etc.



Features

| Model No. | SV 9681.204 |
|--|---|
| Product description | For retrospective external mounting on partial doors. The perforated mounting strips have a 25 mm pitch pattern of holes and may be used for mounting individual accessories such as cable ducts, conduit holders etc. on the rear of the door. Hole diameter of perforated mounting strip: 4.5 mm. |
| Material | Sheet steel, 1 mm |
| Surface finish | Zinc-plated |
| Supply includes | Assembly parts |
| Length | 198 mm |
| Assembly instruction | For 1000 mm enclosure width: 1 x 9681.204 and 1 x 9681.206 |
| Dimensions | Length: 198 mm |
| To fit | Width: 400 mm |
| OUT_SUITABLE_FOR_PARTIAL_DO OR_HEIGHTS | 200 - 800 mm |
| Packs of | 10 pc(s). |
| Net weight | 0.6 |
| PCF per pack (cradle-to-gate) | 2.4 kg CO2 eq (Cat B) |

© Rittal 2025 2

Features

| Note on PCF category | Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared |
|-----------------------|--|
| Customs tariff number | 73269098 |
| EAN | 4028177930353 |
| ETIM 9 | EC000386 |
| ECLASS 8.0 | 27400501 |

Approvals

Explanations Declaration of conformity UK

© Rittal 2025 3