Rittal – The System.

Faster – better – everywhere.





SV 9683.561 Partial mounting plate

State: 03/11/2025 (Source: rittal.com/uae-en)



SV 9683.561 - Partial mounting plate for compartment side panel

With or without duct, for direct attachment to the functional space side panel.

Features

SV 9683.561
with gland made from insulating material
For direct attachment to the compartment side panel for internal compartmentalisation. Universal interior installation with switchgear and controlgear. Creation of additional mounting levels. In combination with compartment dividers and side panel, internal compartmentalisation in accordance with Form 1 to 4 is possible.
Sheet steel, 2 mm
Zinc-plated
Angle brackets and assembly parts
150 mm
Width: 502 mm Height: 143 mm
Width: = 600 mm
1 pc(s).
1.76
1.86
7.1 kg CO2 eq (Cat B)
Category B: PCF value (cradle-to-gate) based on the product weight, approximately calculated and self-declared
94039910
4028177935204
EC000213

© Rittal 2025

Features

ECLASS 8.0

27400613

Approvals

Explanations

Declaration of conformity UK

© Rittal 2025

3