Rittal – The System.

Faster – better – everywhere.





CS 9784.520 Outdoor Basic enclosures

State: 18/11/2025 (Source: rittal.com/uae-en)



CS 9784.520 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles







Features

Model No.	CS 9784.520
Design	Enclosure width 1200 mm has two 600 mm wide mounting panels
Product description	Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.
Material	Aluminium AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and profile half- cylinder, lock BJ 20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy

© Rittal 2025

Features

Dimensions	Width: 1,200 mm
	Height: 1,200 mm
	Depth: 400 mm
Dimensions	Overall height: 1,355 mm
	Rain canopy width: 1,250 mm
	Rain canopy height: 55 mm
	Rain canopy depth: 450 mm
	Clearance width: 512 mm
	Clearance height: 1,112 mm
	Clearance depth: 349 mm
	Height base/plinth: 100 mm
Design Centre bar	With removable centre bar, 2 lockable doors
Type rating to UL 50E	Type 3R
IP protection category to IEC 60 529	IP 55
IK Code	IK10
Basic material	Aluminium
Packs of	1 pc(s).
Net weight	66
Gross weight	67
EAN	4028177569195
ETIM 9	EC000261
ECLASS 8.0	27180101

Approvals

Explanations Declaration of conformity
--

© Rittal 2025 3