

# Rittal – The System.

Faster – better – everywhere.



## CS 9784.520

## Outdoor Basic enclosures

State: 01/04/2026 (Source: [rittal.com/uae-en](http://rittal.com/uae-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# CS 9784.520 - Outdoor Basic enclosures

Single-walled enclosure systems, one-door and two-door. Ready to use in all applications with passive interior installation or minimal heat loss in the outdoor sector. Roof concept with all-round louvred grilles



## Features

Model No.	CS 9784.520
Design	Enclosure width 1200 mm has two 600 mm wide mounting panels
Product description	Outdoor enclosure with 100 mm transport plinth and rain canopy with projections on all sides.
Material	Aluminium AlMg3
Surface finish	Powder-coated UV-resistant pure polyester
Colour	RAL 7035
Supply includes	Single-walled outdoor enclosure, fully preconfigured Basic enclosure with gland plate, three-part 25 mm system punchings in the roof, base, front and in the enclosure depth Front door(s) with door stay, swing lever handle and profile half-cylinder, lock BJ 20027 Transport plinth with screw-fastened trim panels front and rear Rain canopy

# Features

---

Dimensions	Width: 1,200 mm Height: 1,200 mm Depth: 400 mm
Dimensions	Overall height: 1,355 mm Rain canopy width: 1,250 mm Rain canopy height: 55 mm Rain canopy depth: 450 mm Clearance width: 512 mm Clearance height: 1,112 mm Clearance depth: 349 mm Height base/plinth: 100 mm
Design Centre bar	With removable centre bar, 2 lockable doors
Type rating to UL 50E	Type 3R
IP protection category to IEC 60529	IP 55
IK Code	IK10
Basic material	Aluminium
Packs of	1 pc(s).
Net weight	66 kg
Gross weight	67 kg
Customs tariff number	94032080
ETIM 9	EC000261
ECLASS 8.0	27180101

---

# Approvals

---

Explanations	Declaration of conformity
--------------	---------------------------