



# Rittal – The System.

Faster – better – everywhere.



SZ 1485.768  
Interior door

State: 17/07/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE


SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SZ 1485.768 - Interior door for AX plastic enclosures

For reliable access protection. Separation of the operating and equipment levels.



## Features

Model No.	SZ 1485.768
Material	Door and door frame: Sheet steel
Surface finish	Door: Powder-coated, textured paint Door frame: Zinc-plated
Colour	Door: RAL 7035
Supply includes	Door Cam lock with 3 mm double-bit insert Assembly screws
Installation options	In AX plastic, on mounting bosses in the side panels
Note	Standard double-bit lock insert may be exchanged for 27 mm lock inserts, type A
To fit enclosure type	AX plastic
Suitable for width	600 mm
Suitable for height	800 mm
Material thickness - door	1 mm
Door opening angle	105°
Packs of	1 pc(s).

# Features

Net weight	5.32
Gross weight	5.62
Customs tariff number	94039910
EAN	4028177965850
ETIM 9	EC000747
ETIM 8	EC000747
ECLASS 8.0	27182204