

# Rittal – The System.

Faster – better – everywhere.



## KL 1524.010 Terminal boxes KL

State: 12/05/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# KL 1524.010 - Terminal boxes KL Stainless steel

Terminal boxes, stainless steel 1.4301 (AISI 304), Protection category IP 66.

## Features

|                                   |   |
|-----------------------------------|---|
| Model No.                         | KL 1524.010   |
| Material                          | Enclosure: Stainless steel 1.4301 (AISI 304)<br>Cover: Stainless steel 1.4301 (AISI 304), all-round foamed-in PU seal |
| Surface finish                    | Enclosure and cover: Brushed, grain 180   |
| Supply includes                   | Enclosure with cover<br>Quick-release fastener including plastic bushes   |
| Protection category NEMA          | NEMA 4X   |
| Protection category to IEC 60 529 | IP 66   |
| IK Code                           | IK08  |
| Dimensions                        | Width: 300 mm<br>Height: 200 mm<br>Depth: 80 mm   |
| Material thickness - cover        | 1.25 mm   |
| Material thickness - enclosure    | 1.25 mm   |
| Lock                              | Number of locks: 4  |
| Basic material                    | Stainless steel 1.4301 (AISI 304)   |
| Packs of                          | 1 pc(s).  |
| Net weight                        | 2.15 kg   |
| Gross weight                      | 2.28 kg   |
| Customs tariff number             | 84879090  |
| ETIM 9                            | EC000261  |
| ETIM 8                            | EC000261  |
| ECLASS 8.0                        | 27180101  |

# Features

---

|                     |  |
|---------------------|--|
| Product description | KL Terminal box, WHD: 300x200x80 mm, Stainless steel 1.4301, without mounting plate, with cover, without gland plate |
|---------------------|--|

# Approvals

---

|           |  |
|-----------|--|
| Approvals | Bureau Veritas<br>DNV<br>Lloyds Register<br>UL + C-UL (listed) |
|-----------|--|

---

|              |   |
|--------------|---|
| Explanations | Declaration of conformity<br>Declaration of conformity UK |
|--------------|---|

---

# Tender text

Stainless steel terminal box without gland plate, protection cat. IP 66

Enclosure:  
of 1.25 mm stainless steel 1.4301 (AISI 304), folded and welded from a single piece, with all-round protection channel on the cover aperture. Cover of 1.25 mm stainless steel, sealed, with foamed-in special cover seal, facilities for connecting PE conductors in the cover and box, profile strips on both internal sides with mounting holes. Special plastic bush guards against accidental loss of the cover screws and provides screwdriver guidance.

Accessories:  
quick-release fastener, cover retainer, plastic cable gland plate, cover hinges, mounting plate

Surface finish:  
brushed

Dimensions (W x H x D): 300 x 200 x 80 mm