

Rittal – The System.

Faster – better – everywhere.



SG 2372.031

LED steady light component

State: 23/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SG 2372.031 - LED steady light component for signal pillar, modular

With 360° signal transmission thanks to optimised prism system.

Features

Model No.	SG 2372.031
Design	LED steady light component
Benefits	With 360° signal transmission thanks to optimised prism system Configuration of up to five components with the same voltage.
Function principle	A modular layout is possible with connection, optical and acoustic components and a label panel
Material	Enclosure of polyamide Cap: Transparent polycarbonate
Colour	Clear
Protection category to IEC 60 529	IP 65 if a cover or acoustic component is fitted at the top
Rated operating voltage	24 V (AC/DC)
Packs of	1 pc(s).
Net weight	0.07 kg
Gross weight	0.073 kg
Customs tariff number	85311095
ETIM 9	EC000232
ETIM 8	EC000232
ECLASS 8.0	27371220
Product description	SG LED steady light component, clear

Approvals

Approvals

Approvals	UL + C-UL (listed)
Explanations	Declaration of conformity
