

Rittal – The System.

Faster – better – everywhere.



SG 2372.130

Signal pillar LED compact

State: 30/01/2026 (Source: rittal.com/uk-en)



ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP

SG 2372.130 - Signal pillar LED compact

Extremely long service life of the LEDs, minimal assembly work and low warehousing costs.

Features

Model No.	SG 2372.130
Design	1-stage, red
Product description	Transmission angle: 3 x 120°, supplied state: Steady light. Flashing function controllable via PLC
Benefits	Complete, ready-to-connect solution Minimal build height Long LED service life Minimal assembly work and warehousing costs
Cable entry	Min. cable diameter: 3 mm Max. cable diameter: 6.5 mm
Diameter	72 mm
Type of electrical connection	Screw terminals
Light	LEDs
Rated insulation voltage	< 60 V DC
Dimensions	Height: 107 mm
Operating temperature range	-20 °C...70 °C
Protection category to IEC 60 529	IP 65
Rated operating voltage	24 V 24 V (DC)
Packs of	1 pc(s).
Net weight	0.219
Gross weight	0.233
Customs tariff number	85311095
EAN	4028177490130

Features

ECLASS 8.0

27371230

Approvals

Approvals UR

Explanations Declaration of conformity
Declaration of conformity UK