## Rittal - The System.

Faster – better – everywhere.





# AE 2383.300 Rail for interior installation

State: 17/11/2025 (Source: rittal.com/uk-en)



### AE 2383.300 - Rail for interior installation for AE/WM

For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas.



#### **Features**

Model No.	AE 2383.300	
Product description	For mounting in the enclosure, no machining required. Suitable for all-round mounting on the sides, base and roof areas. Variable with 2 rows of system punchings, creates additional mounting space e.g for: TS punched section, enclosure lights, door-operated switch, door stay, cable conduit holder	
Material	Sheet steel	
Surface finish	Zinc-plated	
Note	Other mounting options: Mounting plates, locatable, TS 8612.400 Mounting plates, screw-fastening, large, TS 8612.410 Mounting plates, screw-fastening, small, PS 4532.000 Mounting bracket, PS 4597.000	
To fit	Enclosure type: AE Depth: = 300 mm	
Packs of	4 pc(s).	
Net weight	0.8	
Gross weight	0.92	
Customs tariff number	73269098	
EAN	4028177687431	
E-Number Sweden	E3404334	

© Rittal 2025

#### **Features**

ETIM 9	EC002625	
ETIM 8	EC002625	
ECLASS 8.0	27189234	

© Rittal 2025 3