


Rittal – The System.

Faster – better – everywhere.



AX 2475.010 Protective roof

State: 11/05/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



AX 2475.010 - Protective roof for AX

The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above.



Features

| | |
|-----------------------|--|
| Model No. | AX 2475.010 |
| Product description | The sloping protective roof reliably protects the enclosure from standing moisture and other soiling from above. |
| Material | Stainless steel 1.4301 (AISI 304) |
| Surface finish | Brushed, grain 240 |
| Supply includes | Assembly parts |
| Installation options | May also be screw-fastened for dynamic loads |
| Dimensions | Height: 43 mm |
| Type rating to UL 50E | Type 1 Type 3R Type 4 Type 4X Type 12 |
| To fit | Enclosure type: AX Width: = 800 mm Depth: = 300 mm |
| Packs of | 1 pc(s). |
| Net weight | 3.56 kg |

Features

| | |
|-----------------------|---|
| Gross weight | 4.02 kg |
| Customs tariff number | 94039910 |
| ETIM 9 | EC000744 |
| ETIM 8 | EC000744 |
| ECLASS 8.0 | 27182405 |
| Product description | AX Protective roof, for WD: 800x300 mm, stainless steel |

Approvals

| | |
|-----------|------------------|
| Approvals | UL + C-UL - FTTA |
|-----------|------------------|
