## Rittal - The System.

Faster – better – everywhere.





# SZ 2563.500 Plastic cable gland plates

State: 8/12/2025 (Source: rittal.com/uk-en)



## SZ 2563.500 - Plastic cable gland plates with membranes

Simply pierce the plastic and pull through the cable, protection category IP 65 with careful cable entry.

#### **Features**

Model No.	SZ 2563.500	
Product description	Simply pierce the plastic with a sharp object, and pull through the cable.	
Material	Plastic to UL 94-V0 Halogen free	
Colour	Similar to RAL 7035	
Note	The allocation of gland plate sizes is indicated on the relevant enclosures	
Dimensions	Width: 534 mm Depth: 149 mm	
To fit	Enclosure type: AE	
Gland plate	Size: 5	
Protection category to IEC 60 529	IP 65	
No. of cable entries and Ø (mm) minmax.	18 x 5-9 16 x 7-12 36 x 10-15 6 x 15-24 2 x 23-30 2 x 26-35 4 x 26-54 1 x 50-110	
Packs of	1 pc(s).	
Net weight	0.86	
Gross weight	0.96	
Customs tariff number	39269097	
EAN	4028177325616	

© Rittal 2025

#### **Features**

E-Number Sweden	E3404729	
ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

© Rittal 2025 3