Rittal - The System.

Faster – better – everywhere.






SZ 2566.200 Plastic gland plate, modular

State: 4/11/2025 (Source: rittal.com/uk-en)



SZ 2566.200 - Plastic gland plate, modular with metric knockouts, for AX

Simply break through the plastic on the knockouts for cable glands. Additional rectangular cutouts and reinforcement frame allow the cable gland to be installed directly (modular).







Features

Model No.	SZ 2566.200	
Product description	Simply break through the plastic on the knockouts for cable glands. Additional rectangular cut-outs and reinforcement frame allow the cable gland to be installed directly (modular).	
Material	Plastic to UL 94-V0	
Colour	RAL 7035	
Number of rectangular cutouts information	1 rectangular cut-out can hold 10 small seal inserts	
Number of rectangular cutouts	6	
Note	The allocation of gland plate sizes is indicated on the relevant enclosures	

© Rittal 2025 2

Features

No. of metric knockouts	4 x M12
	5 x M16
	5 x M20
	4 x M25
	1 x M32
	1 x M40
	1 x M50
Dimensions	Width: 401 mm
	Depth: 221 mm
To fit	Enclosure type: AX
Gland plate	Size: 6
Operating temperature range	-40 °C80 °C
Protection category to IEC 60 529	IP 66 if installed correctly
Type rating to UL 50E	Type 1
	Type 12
Number knockouts	4
	5
	5
	4
	1
	1
	1
Metric diameter	M12
	M16
	M20
	M25
	M32
	M40
	M50
Packs of	1 pc(s).
Net weight	0.5
Gross weight	0.56
Customs tariff number	39269097
EAN	4028177938441

© Rittal 2025 3

Features

ETIM 9	EC000211	
ETIM 8	EC000211	
ECLASS 8.0	27142421	

Approvals

Approvals UL + C-UL - FTTA

© Rittal 2025