## Rittal – The System.

Faster – better – everywhere.





# TP 2695.500 Universal consoles TP

State: 9/12/2025 (Source: rittal.com/uk-en)



#### TP 2695.500 - Universal consoles TP

Universal consoles TP, high level of stability and protection category IP 55 because the body is more or less manufactured from a single piece. Flexible front design, optionally with drawers or desk section. Easy accessibility thanks to divided doors. Interchangeable lock insert.

#### **Features**

Model No.	TP 2695.500
Design	with tall front door
Product modification	The universal console comes with the new mounting plate of the baying enclosure system VX25.
Material	Enclosure, gland plates: Sheet steel 1.5 mm Door: Sheet steel, 2.0 mm Mounting plate: Sheet steel, 3.0 mm
Surface finish	Enclosure and door: Dipcoat primed, powder-coated on the outside, textured paint Mounting plate and gland plates: Zinc-plated
Colour	RAL 7035
Supply includes	Enclosure with door(s) Mounting plate Gland plates
Dimensions	Width: 600 mm Height: 1,300 mm
Dimensions mounting plate (W x H)	499 mm x 1,196 mm
Depth (top)	417.5 mm
Depth (bottom)	500 mm
IK Code	IK08
Note	For universal console with short front door: The desk section should be fitted in order to maintain the protection category.
IP protection category to IEC 60 529	IP 55

© Rittal 2025 2

### Features

Protection category NEMA	NEMA 12
Basic material	Sheet steel
Dimensions	Width: 600 mm
	Height: 1,300 mm Depth (top): 417.5 mm
	Depth (bottom): 500 mm
Packs of	1 pc(s).
Net weight	74.1
Gross weight	78
Customs tariff number	94032080
EAN	4028177031548
ETIM 9	EC000784
ETIM 8	EC000784
ECLASS 8.0	27180504

## Approvals

Approvals	TÜV UL + C-UL (listed)
Explanations	Declaration of conformity  Declaration of conformity UK

© Rittal 2025 3