

# Rittal – The System.

Faster – better – everywhere.



## FT 2736.520 System windows

State: 30/08/2025 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# FT 2736.520 - System windows for VX, TS, VX SE

To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.



## Features

|                     |   |
|---------------------|---|
| Model No.           | FT 2736.520   |
| Design              | 60 section  |
| Product description | To conceal display and operating instruments or cut-outs, and to protect against dirt and liquids as well as unauthorised access.   |
| Material            | Extruded aluminium section with die-cast zinc corner pieces and single-pane safety glass.   |
| Surface finish      | Base frame: Powder-coated on the outside in RAL 7035<br>Hinge and lock section: Natural-anodised  |
| Value base frame    | Made from single-pane safety glass: High level of resistance to solvents and scratches, anti-static, reduced risk of injury if broken. Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).<br>Hinge with 180° opening angle, easily inserted. |

# Features

|                                   |  |
|-----------------------------------|--|
| Value base frame                  | <p>Easily screw-fastened to the door thanks to modified dimensions (tubular door frame may be used as a drilling template).</p> <p>Readily height-adjustable.</p> <p>Stabilises the door cut-out.</p> <p>Conceals the cut edge.</p> <p>There is no dirt on the seal, the glass is protected from being lifted out, dirt cannot drop inside, and moisture cannot run behind the window when opening.</p> <p>Frame section height 30 mm or 60 mm</p> |
| Protection category to IEC 60 529 | IP 54  |
| Note                              | <p>Standard double-bit lock insert may be exchanged for lock inserts 27 mm, type A, and/or for lock system Ergoform-S (except H = 270 mm).</p> <p>Not suitable for outdoor siting</p>  |
| To fit                            | <p>Enclosure type: VX</p> <p>TS</p> <p>VX SE</p> <p>Width: = 600 mm</p>  |
| Dimensions                        | <p>Width: 500 mm</p> <p>Height: 470 mm</p> <p>Depth: 77 mm</p>   |
| Visible area                      | <p>Viewing window width: 363 mm</p> <p>Viewing window height: 398 mm</p>   |
| Build depth for components (max.) | 63 mm  |
| Packs of                          | 1 pc(s).   |
| Net weight                        | 5.178  |
| Gross weight                      | 5.45   |
| Customs tariff number             | 76101000   |
| EAN                               | 4028177476424  |
| ETIM 9                            | EC002527   |
| ETIM 8                            | EC002527   |
| ECLASS 8.0                        | 27182301   |

# Approvals

---

Certificates

Protection category