

Rittal – The System.

Faster – better – everywhere.



SZ 2899.200 Stepped collar

State: 23/02/2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SZ 2899.200 - Stepped collar For wall thicknesses from 1.5 to 4.5 mm

For cable entry, simply cut off at the required level to match the cable diameter.



Features

| | |
|-------------------------------------|--|
| Model No. | SZ 2899.200 |
| Product description | For cable entry, simply cut off at the required level to match the cable diameter. |
| Applications | For wall thicknesses from 1.5 to 4.5 mm |
| Material | Cover: Thermoplastic elastomer |
| Dimensions | Thread: M20 |
| For wall thickness (max.) | 1.5 - 4.5 mm |
| IP protection category to IEC 60529 | IP 54 with careful cable entry |
| For cable diameters | 5 - 16 mm |
| Packs of | 100 pc(s). |
| Net weight | 0.2 kg |
| Gross weight | 0.252 kg |
| Customs tariff number | 39269097 |
| ETIM 9 | EC000879 |
| ETIM 8 | EC000879 |
| ECLASS 8.0 | 27069216 |

Features

Product description

SZ Stepped collar, for wall thickness from 1,5 bis 4,5 mm, for hole M20, Sealing range: 5-16 mm