

Rittal – The System.

Faster – better – everywhere.



SV 3087.000 System cover

State: 23.05.2026 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SV 3087.000 - System cover

For conductor connection clamps and plate clamps.

Features

Model No.	SV 3087.000
Product description	For conductor connection clamps and plate clamps.
Material	ABS Fire protection corresponding to UL 94-V0
Colour	RAL 7035
Height when mounted on 60 mm busbar systems	230 mm
Height when mounted on 100 mm busbar systems	325 mm
Note	For 3-pole systems with 60/100 mm bar centre distance Only suitable for use with systems without a base tray For systems with a base tray, the system covers must be mechanically shortened
Dimensions	Width: 100 mm Depth: 80 mm
Packs of	4 pc(s).
Net weight	1.2 kg
Gross weight	1.384 kg
Customs tariff number	85472000
ETIM 9	EC000775
ETIM 8	EC000775
ECLASS 8.0	27142414
Product description	SV System cover, WD: 100x80 mm, H: 230-325 mm

Tender text

System covers

for conductor connection clamps and plate clamps (according to VBG 4). Suitable for 60 und 100 mm busbar systems.

Width: 100 mm

Height: 80 mm

Material: ABS

Continuous operating temperature: max. 100 °C

Fire protection: corresponding to UL 94-V0