

Rittal – The System.

Faster – better – everywhere.



SK 3164.230

Roof-mounted fans

State: 6/07/2025 (Source: rittal.com/uk-en)

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



SK 3164.230 - Roof-mounted fans for VX, VX IT

Roof-mounted fan for the office sector with exceptionally low noise level (40 dB) and high volumetric flow (unimpeded air flow 1500 m³/h).



Features

| | |
|--------------------------------------|--|
| Model No. | SK 3164.230 |
| Benefits | Easy assembly, the roof plate variant eliminates the need to create mounting cut-outs Fully wired ready for connection |
| Material | Sheet steel, spray-finished |
| Colour | RAL 7035 |
| Supply includes | Roof-mounted fans Assembly parts |
| Rated operating voltage | 230 V, 1~, 50 Hz/60 Hz |
| Rated current max. | At 50 Hz: 0.3 A At 60 Hz: 0.35 A |
| Dimensions | Width: 511 mm Height: 227 mm Depth: 511 mm |
| IP protection category to IEC 60 529 | Internal circuit IP 54 |
| Note | Reduction in the specified air throughput to 800 m ³ /h at 40 Pa counterpressure using two vented base/plinth trim panels |
| Operating temperature range | 20 °C...55 °C |
| Packs of | 1 pc(s). |

Features

| | |
|-----------------------|---------------|
| Net weight | 18.35 |
| Gross weight | 19.36 |
| Customs tariff number | 84145915 |
| EAN | 4028177309494 |
| ECLASS 8.0 | 27180716 |

Approvals

| | |
|--------------|---|
| Certificates | EAC |
| Explanations | Declaration of conformity Declaration of conformity UK |