

**Rittal – The System.**

Faster – better – everywhere.



**SK 3238.066**

**Chopped-fibre filter mat**

State: 10/06/2026 (Source: [rittal.com/uk-en](http://rittal.com/uk-en))

ENCLOSURES

POWER DISTRIBUTION

CLIMATE CONTROL

IT INFRASTRUCTURE

SOFTWARE & SERVICES

FRIEDHELM LOH GROUP



# SK 3238.066 - Chopped-fibre filter mat

Spare filter mats for roof-mounted fans, fan-and-filter units or thermoelectric coolers, for effective protection of enclosure components from dirt, dust and water.

## Features

Model No.	SK 3238.066
Design	for EMC filter fans
Product description	Made of chopped-fibre mat with a progressive structure. Temperature-resistant to 100 °C, self-extinguishing category F1 to DIN 53 438. Dust-laden air side: Open structure. Clean-air side: Closed structure. Reliable filtering of virtually all types of dust from a particle size of 10 µm.
Material	Copper-nickel-chrome coated chemical fibres
Note	Performance data, protection category and device approvals are only guaranteed when used in conjunction with original Rittal filter mats.
To fit Model No.	3238.6..
Dimensions	Width: 125 mm Height: 125 mm Depth: 12 mm
Filter class	to DIN EN 779: G2
Packs of	5 pc(s).
Net weight	0.015 kg
Gross weight	0.02 kg
Customs tariff number	56039390
ETIM 9	EC002513
ETIM 8	EC002513
ECLASS 8.0	27180706
Product description	SK spare filter mats, for EMC-filter fans, for SK 3238.6.., WHD: 125 x 125 x 12 mm

# Approvals

---

Approvals

CSA

UR + C-UR (recognized)